



Slotted countersunk head screw DIN 963 Stainless steel A4 70 M6X18

Article number	55110.060.018
Brand	-
UBB	500571382869
UNSPSC	31161504
EAN	8715494130219
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M6
Length	18 mm
Class	70
Driving features	Slotted
Head shape	Countersunk head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NF	≈E25-123
BS	≈4183
NEN	≈2370
ASME	≈B18.6.7M
ISO	≈2009
DIN	963

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
Full thread if $L \leq$	35
k (max.)	3
L (mm)	18
n	1.6
P	1
t (min.)	1.2

Technical Drawing

