

Slotted countersunk head screw DIN 963 Stainless steel A4 70 M6X40



Article number	55110.060.040
Brand	-
UBB	950353294578
UNSPSC	31161504
EAN	8715492334077
PKG. of 200	Full Box Only

Technical Parameters

Diameter (d-D)	M6
Length (L) (mm)	40
Class	70
Material	Stainless steel
Head shape	Countersunk head
Driving features	Slotted
Thread	Metric thread
Material technical	A4

Standards

ISO	≈2009
DIN	963
ASME	≈B18.6.7M
NF	≈E25-123
BS	≈4183

Technical Specification

Thread length (min.)	28
d_k (max.)	11
Full thread if $L \leq$	35
k (max.)	3
n	1.6
P	1
t (min.)	1.2

Technical Drawing

