



Slotted countersunk head screw DIN 963 Stainless steel A4 70 M6X100

Article number	55110.060.100
Brand	-
UBB	950353564434
UNSPSC	31161504
EAN	8715492334145
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M6
Length	100 mm
Class	70
Driving features	Slotted
Head shape	Countersunk head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NF	≈E25-123
NEN	≈2370
DIN	963
ASME	≈B18.6.7M
ISO	≈2009
BS	≈4183

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
Full thread if $L \leq$	35
k (max.)	3
L (mm)	100
n	1.6
P	1
t (min.)	1.2

Technical Drawing

