



Slotted countersunk head screw DIN 963 Stainless steel A4 70 M8X55

Article number	55110.080.055
Brand	-
UBB	500571383362
UNSPSC	31161504
EAN	8715494130264
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	55 mm
Class	70
Driving features	Slotted
Head shape	Countersunk head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NEN	≈2370
ISO	≈2009
ASME	≈B18.6.7M
NF	≈E25-123
BS	≈4183
DIN	963

Technical Specification

d-D	M8
Thread length (min.)	34
dk (max.)	14.5
Full thread if $L \leq$	40
k (max.)	4
L (mm)	55
n	2
P	1.25
t (min.)	1.6

Technical Drawing

