



Slotted countersunk head screw DIN 963 Stainless steel A4 70 M8X60

Article number	55110.080.060
Brand	-
UBB	950353295807
UNSPSC	31161504
EAN	8715492334244
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	60 mm
Class	70
Driving features	Slotted
Head shape	Countersunk head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NF	≈E25-123
ISO	≈2009
ASME	≈B18.6.7M
DIN	963
BS	≈4183
NEN	≈2370

Technical Specification

d-D	M8
Thread length (min.)	34
dk (max.)	14.5
Full thread if $L \leq$	40
k (max.)	4
L (mm)	60
n	2
P	1.25
t (min.)	1.6

Technical Drawing

