

Slotted countersunk head screw DIN 963 Stainless steel A4 70 M10X35



Article number	55110.100.035
Brand	-
UBB	950353296557
UNSPSC	31161504
EAN	8715492334329
PKG. of 100	Full Box Only

Technical Parameters

Diameter (d-D)	M10
Length (L) (mm)	35
Class	70
Material	Stainless steel
Head shape	Countersunk head
Driving features	Slotted
Thread	Metric thread
Material technical	A4

Standards

NF	≈E25-123
BS	≈4183
DIN	963
ISO	≈2009
ASME	≈B18.6.7M

Technical Specification

Thread length (min.)	40
d_k (max.)	18
Full thread if $L \leq$	50
k (max.)	5
n	2.5
P	1.50
t (min.)	2

Technical Drawing

