



Slotted countersunk head screw DIN 963 Stainless steel A4 70 M12X80

Article number	55110.120.080
Brand	-
UBB	950353297886
UNSPSC	31161504
EAN	8715492334480
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M12
Length	80 mm
Class	70
Driving features	Slotted
Head shape	Countersunk head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

ISO	≈2009
DIN	963
NF	≈E25-123
ASME	≈B18.6.7M
BS	≈4183
NEN	≈2370

Technical Specification

d-D	M12
Thread length (min.)	46
dk (max.)	22
Full thread if $L \leq$	60
k (max.)	6
L (mm)	80
n	3
P	1.75
t (min.)	2.4

Technical Drawing

