

## Slotted countersunk head screw DIN 963 A Stainless steel A4 M16X25



Article number	55110.160.025
Brand	-
UBB	500571384501
UNSPSC	31161504
EAN	8715494127837
PKG. of 25	Full Box Only

### Technical Parameters

Diameter (d-D)	M16
Length (L) (mm)	25
Material	Stainless steel
Head shape	Countersunk head
Driving features	Slotted
Thread	Metric thread
Material technical	A4

### Standards

DIN	963 A
NF	E25-123
BS	4183
ISO	2009
ASME	B18.6.7M

### Technical Specification

Thread length (min.)	58
$d_k$ (max.)	29
Full thread if $L \leq$	70
k (max.)	8
n	5
P	2
t (min.)	3.2

### Technical Drawing

