

Slotted cheese head screw DIN 84 Stainless steel A4 70 M1,6X4



Article number	55120.016.004
Brand	-
UBB	500571385839
UNSPSC	31161504
EAN	8715494127967
PKG. of 1000	Full Box Only

Technical Parameters

Diameter (d-D)	M1,6
Length (L) (mm)	4
Class	70
Material	Stainless steel
Head shape	Cylindrical head
Driving features	Slotted
Thread	Metric thread
Material technical	A4

Standards

NF	≈E25-127
BS	≈4183
ISO	≈1207
DIN	84
ASME	≈B18.6.7M

Technical Specification

Thread length (min.)	25
d_k (max.)	3
Full thread if $L \leq$	30
k (max.)	1
n	0.4
P	0.35
t (min.)	0.45

Technical Drawing