



Slotted cheese head screw DIN 84 Stainless steel A4 70 M2X10

Article number	55120.020.010
Brand	-
UBB	950353298538
UNSPSC	31161504
EAN	8715492334572
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M2
Length	10 mm
Class	70
Driving features	Slotted
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

DIN	84
BS	≈4183
ISO	≈1207
ASME	≈B18.6.7M
NEN	≈1602
NF	≈E25-127

Technical Specification

d-D	M2
Thread length (min.)	25
dk (max.)	3.8
Full thread if L ≤	30
k (max.)	1.3
L (mm)	10
n	0.5
P	0.4
t (min.)	0.5

Technical Drawing