

Slotted cheese head screw DIN 84 Stainless steel A4 M2,5X16



Article number	55120.025.016
Brand	-
UBB	950353299452
UNSPSC	31161504
EAN	8715492334749
PKG. of 500	Full Box Only

Technical Parameters

Diameter (d-D)	M2,5
Length (L) (mm)	16
Class	70
Material	Stainless steel
Head shape	Cylindrical head
Driving features	Slotted
Thread	Metric thread
Material technical	A4

Standards

DIN	84
ASME	≈B18.6.7M
ISO	≈1207
BS	≈4183
NF	≈E25-127

Technical Specification

Thread length (min.)	25
d_k (max.)	4.5
Full thread if $L \leq$	30
k (max.)	1.6
n	0.6
P	0.45
t (min.)	0.7

Technical Drawing