

## Slotted cheese head screw DIN 84 Stainless steel A4 M3X5



Article number	55120.030.005
Brand	-
UBB	950353299601
UNSPSC	31161504
EAN	8715492334787
PKG. of 500	Full Box Only

### Technical Parameters

Diameter (d-D)	M3
Length (L) (mm)	5
Class	70
Material	Stainless steel
Head shape	Cylindrical head
Driving features	Slotted
Thread	Metric thread
Material technical	A4

### Standards

ASME	≈B18.6.7M
ISO	≈1207
BS	≈4183
DIN	84
NF	≈E25-127

### Technical Specification

Thread length (min.)	25
$d_k$ (max.)	5.5
Full thread if $L \leq$	30
$k$ (max.)	2
$n$	0.8
$P$	0.50
$t$ (min.)	0.85

### Technical Drawing