

Slotted cheese head screw DIN 84 Stainless steel A4 M3X12



Article number	55120.030.012
Brand	-
UBB	950353336817
UNSPSC	31161504
EAN	8715492334824
PKG. of 500	Full Box Only

Technical Parameters

Diameter (d-D)	M3
Length (L) (mm)	12
Class	70
Material	Stainless steel
Head shape	Cylindrical head
Driving features	Slotted
Thread	Metric thread
Material technical	A4

Standards

ISO	≈1207
NF	≈E25-127
DIN	84
BS	≈4183
ASME	≈B18.6.7M

Technical Specification

Thread length (min.)	25
d_k (max.)	5.5
Full thread if $L \leq$	30
k (max.)	2
n	0.8
P	0.50
t (min.)	0.85

Technical Drawing