



Slotted cheese head screw DIN 84 Stainless steel A4 70 M3X35

Article number	55120.030.035
Brand	-
UBB	950353470871
UNSPSC	31161504
EAN	8715492334916
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	35 mm
Class	70
Driving features	Slotted
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NF	≈E25-127
ASME	≈B18.6.7M
NEN	≈1602
DIN	84
BS	≈4183
ISO	≈1207

Technical Specification

d-D	M3
Thread length (min.)	25
dk (max.)	5.5
Full thread if L ≤	30
k (max.)	2
L (mm)	35
n	0.8
P	0.5
t (min.)	0.85

Technical Drawing