



Slotted cheese head screw DIN 84 Stainless steel A4 70 M4X28

Article number	55120.040.028
Brand	-
UBB	500571388494
UNSPSC	31161504
EAN	8715494128223
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	28 mm
Class	70
Driving features	Slotted
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

DIN	84
BS	≈4183
ASME	≈B18.6.7M
NF	≈E25-127
ISO	≈1207
NEN	≈1602

Technical Specification

d-D	M4
Thread length (min.)	38
dk (max.)	7
Full thread if L ≤	40
k (max.)	2.6
L (mm)	28
n	1.2
P	0.7
t (min.)	1.1

Technical Drawing