



Slotted cheese head screw DIN 84 Stainless steel A4 70 M6X22

Article number	55120.060.022
Brand	-
UBB	500571388981
UNSPSC	31161504
EAN	8715494128278
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	22 mm
Class	70
Driving features	Slotted
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NEN	≈1602
DIN	84
BS	≈4183
NF	≈E25-127
ASME	≈B18.6.7M
ISO	≈1207

Technical Specification

d-D	M6
Thread length (min.)	38
dk (max.)	10
Full thread if L ≤	40
k (max.)	3.9
L (mm)	22
n	1.6
P	1
t (min.)	1.6

Technical Drawing