



**Slotted cheese head screw
DIN 84 Stainless steel A4 70
M6X55**

Article number	55120.060.055
Brand	-
UBB	500571389062
UNSPSC	31161504
EAN	8715494128285
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	55 mm
Class	70
Driving features	Slotted
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NF	≈E25-127
NEN	≈1602
DIN	84
ASME	≈B18.6.7M
ISO	≈1207
BS	≈4183

Technical Specification

d-D	M6
Thread length (min.)	38
dk (max.)	10
Full thread if L ≤	40
k (max.)	3.9
L (mm)	55
n	1.6
P	1
t (min.)	1.6

Technical Drawing