



Slotted cheese head screw DIN 84 Stainless steel A4 70 M10X70

Article number	55120.100.070
Brand	-
UBB	950353306463
UNSPSC	31161504
EAN	8715492335807
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Length	70 mm
Class	70
Driving features	Slotted
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NF	≈E25-127
DIN	84
NEN	≈1602
BS	≈4183
ASME	≈B18.6.7M
ISO	≈1207

Technical Specification

d-D	M10
Thread length (min.)	38
dk (max.)	16
Full thread if L ≤	40
k (max.)	6
L (mm)	70
n	2.5
P	1.5
t (min.)	2.5

Technical Drawing