



Slotted cheese head screw DIN 84 Stainless steel A4 70 M10X100

Article number	55120.100.100
Brand	-
UBB	950353306794
UNSPSC	31161504
EAN	8715492335838
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Length	100 mm
Class	70
Driving features	Slotted
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NF	≈E25-127
ASME	≈B18.6.7M
BS	≈4183
NEN	≈1602
ISO	≈1207
DIN	84

Technical Specification

d-D	M10
Thread length (min.)	38
dk (max.)	16
Full thread if L ≤	40
k (max.)	6
L (mm)	100
n	2.5
P	1.5
t (min.)	2.5

Technical Drawing