



Slotted pan head screw DIN 85 Stainless steel A4 70 M2X8

Article number	55140.020.008
Brand	-
UBB	500571517357
UNSPSC	31161504
EAN	8715494096638
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M2
Length	8 mm
Class	70
Driving features	Slotted
Head shape	Pan head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

BS	≈4183
ASME	≈B18.6.7M
DIN	85
ISO	≈1580
NEN	≈1603
NF	≈E25-128

Technical Specification

d-D	M2
Thread length (min.)	25
dk (max.)	4
Full thread if $L \leq$	16
k (max.)	1.3
L (mm)	8
n	0.5
P	0.4
t (min.)	0.5

Technical Drawing

