



Slotted pan head screw DIN 85 Stainless steel A4 70 M2,5X6

Article number	55140.025.006
Brand	-
UBB	500571517506
UNSPSC	31161504
EAN	8715494096652
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M2.5
Length	6 mm
Class	70
Driving features	Slotted
Head shape	Pan head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NEN	≈1603
DIN	85
BS	≈4183
ISO	≈1580
ASME	≈B18.6.7M
NF	≈E25-128

Technical Specification

d-D	M2.5
Thread length (min.)	25
dk (max.)	5
Full thread if $L \leq$	16
k (max.)	1.5
L (mm)	6
n	0.6
P	0.45
t (min.)	0.6

Technical Drawing

