



Slotted pan head screw DIN 85 Stainless steel A4 70 M2,5X8

Article number	55140.025.008
Brand	-
UBB	500571517688
UNSPSC	31161504
EAN	8715494096669
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M2.5
Length	8 mm
Class	70
Driving features	Slotted
Head shape	Pan head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

BS	≈4183
NEN	≈1603
ISO	≈1580
NF	≈E25-128
ASME	≈B18.6.7M
DIN	85

Technical Specification

d-D	M2.5
Thread length (min.)	25
dk (max.)	5
Full thread if $L \leq$	16
k (max.)	1.5
L (mm)	8
n	0.6
P	0.45
t (min.)	0.6

Technical Drawing

