



Slotted pan head screw DIN 85 Stainless steel A4 70 M3X16

Article number	55140.030.016
Brand	-
UBB	950353307529
UNSPSC	31161504
EAN	8715492335913
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	16 mm
Class	70
Driving features	Slotted
Head shape	Pan head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

ASME	≈B18.6.7M
ISO	≈1580
NF	≈E25-128
DIN	85
BS	≈4183
NEN	≈1603

Technical Specification

d-D	M3
Thread length (min.)	25
dk (max.)	6
Full thread if $L \leq$	30
k (max.)	1.8
L (mm)	16
n	0.8
P	0.5
t (min.)	0.7

Technical Drawing

