



Slotted pan head screw DIN 85 Stainless steel A4 70 M3X25

Article number	55140.030.025
Brand	-
UBB	950353307784
UNSPSC	31161504
EAN	8715492335937
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	25 mm
Class	70
Driving features	Slotted
Head shape	Pan head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NF	≈E25-128
BS	≈4183
ASME	≈B18.6.7M
DIN	85
ISO	≈1580
NEN	≈1603

Technical Specification

d-D	M3
Thread length (min.)	25
dk (max.)	6
Full thread if $L \leq$	30
k (max.)	1.8
L (mm)	25
n	0.8
P	0.5
t (min.)	0.7

Technical Drawing

