



Slotted pan head screw DIN 85 Stainless steel A4 70 M4X6

Article number	55140.040.006
Brand	-
UBB	950353307867
UNSPSC	31161504
EAN	8715492335968
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	6 mm
Class	70
Driving features	Slotted
Head shape	Pan head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

ASME	≈B18.6.7M
BS	≈4183
NEN	≈1603
DIN	85
ISO	≈1580
NF	≈E25-128

Technical Specification

d-D	M4
Thread length (min.)	38
dk (max.)	8
Full thread if $L \leq$	40
k (max.)	2.4
L (mm)	6
n	1.2
P	0.7
t (min.)	1

Technical Drawing

