



Slotted pan head screw DIN 85 Stainless steel A4 70 M4X25

Article number	55140.040.025
Brand	-
UBB	950353308444
UNSPSC	31161504
EAN	8715492336026
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	25 mm
Class	70
Driving features	Slotted
Head shape	Pan head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NEN	≈1603
ASME	≈B18.6.7M
DIN	85
NF	≈E25-128
ISO	≈1580
BS	≈4183

Technical Specification

d-D	M4
Thread length (min.)	38
dk (max.)	8
Full thread if $L \leq$	40
k (max.)	2.4
L (mm)	25
n	1.2
P	0.7
t (min.)	1

Technical Drawing

