



Slotted pan head screw DIN 85 Stainless steel A4 70 M4X40

Article number	55140.040.040
Brand	-
UBB	950353308774
UNSPSC	31161504
EAN	8715492336057
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	40 mm
Class	70
Driving features	Slotted
Head shape	Pan head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

ASME	≈B18.6.7M
DIN	85
BS	≈4183
NF	≈E25-128
NEN	≈1603
ISO	≈1580

Technical Specification

d-D	M4
Thread length (min.)	38
dk (max.)	8
Full thread if $L \leq$	40
k (max.)	2.4
L (mm)	40
n	1.2
P	0.7
t (min.)	1

Technical Drawing

