



Slotted pan head screw DIN 85 Stainless steel A4 70 M5X20

Article number	55140.050.020
Brand	-
UBB	950353309277
UNSPSC	31161504
EAN	8715492336101
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	20 mm
Class	70
Driving features	Slotted
Head shape	Pan head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

DIN	85
ASME	≈B18.6.7M
ISO	≈1580
BS	≈4183
NF	≈E25-128
NEN	≈1603

Technical Specification

d-D	M5
Thread length (min.)	38
dk (max.)	10
Full thread if $L \leq$	40
k (max.)	3
L (mm)	20
n	1.2
P	0.8
t (min.)	1.2

Technical Drawing

