



Slotted pan head screw DIN 85 Stainless steel A4 70 M6X8

Article number	55140.060.008
Brand	-
UBB	500571518421
UNSPSC	31161504
EAN	8715494096744
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M6
Length	8 mm
Class	70
Driving features	Slotted
Head shape	Pan head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

ISO	≈1580
DIN	85
ASME	≈B18.6.7M
NF	≈E25-128
NEN	≈1603
BS	≈4183

Technical Specification

d-D	M6
Thread length (min.)	38
dk (max.)	12
Full thread if $L \leq$	40
k (max.)	3.6
L (mm)	8
n	1.6
P	1
t (min.)	1.4

Technical Drawing

