



## Slotted pan head screw DIN 85 Stainless steel A4 70 M6X35

|                |               |
|----------------|---------------|
| Article number | 55140.060.035 |
| Brand          | -             |
| UBB            | 950353477074  |
| UNSPSC         | 31161504      |
| EAN            | 8715492336255 |
| PKG. of 200    | Full Box Only |

### Technical Parameters

|                    |                 |
|--------------------|-----------------|
| Diameter           | M6              |
| Length             | 35 mm           |
| Class              | 70              |
| Driving features   | Slotted         |
| Head shape         | Pan head        |
| Material           | Stainless steel |
| Material technical | A4              |
| Thread             | Metric thread   |

### Standards

|      |           |
|------|-----------|
| BS   | ≈4183     |
| NF   | ≈E25-128  |
| NEN  | ≈1603     |
| ASME | ≈B18.6.7M |
| DIN  | 85        |
| ISO  | ≈1580     |

### Technical Specification

|                         |     |
|-------------------------|-----|
| d-D                     | M6  |
| Thread length (min.)    | 38  |
| dk (max.)               | 12  |
| Full thread if $L \leq$ | 40  |
| k (max.)                | 3.6 |
| L (mm)                  | 35  |
| n                       | 1.6 |
| P                       | 1   |
| t (min.)                | 1.4 |

### Technical Drawing

