

Hexagon nut MF DIN 934 Stainless steel A4 70 M10X1,25

Article number	55160.100.125
Brand	-
UBB	950355747300
UNSPSC	31161727
EAN	8715492336415
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Class	70
Driving features	Hexagon
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric fine thread
Info	Sizes with a diameter M20 are minimal property class 50.

Standards

DIN	934
NEN	1560
NF	E25-401

Technical Specification

d-D	M10
m	8
P	1.25
s	17

Technical Drawing

