

Hexagon nut MF DIN 934 Stainless steel A4 Min.50 M27X1,50

Article number	55160.270.150
Brand	-
UBB	500571389302
UNSPSC	31161727
EAN	8715494128315
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M27
Class	Min.50
Driving features	Hexagon
Material	Stainless steel
Material technical	A4
Thread direction	Right
Thread	Metric fine thread
Info	Sizes with a diameter M20 are minimal property class 50.

Standards

NEN	1560
DIN	934
NF	E25-401

Technical Specification

d-D	M27
m	22
P	1.5
s	41

Technical Drawing

