



Slotted raised countersunk head screw DIN 964 Stainless steel A4 70 M2X20

Article number	55210.020.020
Brand	-
UBB	950353583327
UNSPSC	31161504
EAN	8715492336774
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M2
Length	20 mm
Class	70
Driving features	Slotted
Head shape	Countersunk oval head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NF	≈E25-124
DIN	964
NEN	≈2371
BS	≈4183
ISO	≈2010
ASME	≈B18.6.7M

Technical Specification

d-D	M2
Thread length (min.)	16
dk (max.)	3.8
f ≈	0.5
Full thread if L ≤	18
k (max.)	1.2
L (mm)	20
n	0.5
P	0.4
t (min.)	0.8

Technical Drawing

