



Slotted raised countersunk head screw DIN 964 Stainless steel A4 70 M2,5X8

Article number	55210.025.008
Brand	-
UBB	950353583574
UNSPSC	31161504
EAN	8715492336798
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M2.5
Length	8 mm
Class	70
Driving features	Slotted
Head shape	Countersunk oval head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

ISO	≈2010
NF	≈E25-124
ASME	≈B18.6.7M
BS	≈4183
NEN	≈2371
DIN	964

Technical Specification

d-D	M2.5
Thread length (min.)	18
dk (max.)	4.7
f ≈	0.6
Full thread if L ≤	20
k (max.)	1.5
L (mm)	8
n	0.6
P	0.45
t (min.)	1

Technical Drawing

