



Slotted raised countersunk head screw DIN 964 Stainless steel A4 70 M2,5X12

Article number	55210.025.012
Brand	-
UBB	950353583731
UNSPSC	31161504
EAN	8715492336811
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M2.5
Length	12 mm
Class	70
Driving features	Slotted
Head shape	Countersunk oval head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

ASME	≈B18.6.7M
ISO	≈2010
DIN	964
BS	≈4183
NF	≈E25-124
NEN	≈2371

Technical Specification

d-D	M2.5
Thread length (min.)	18
dk (max.)	4.7
f ≈	0.6
Full thread if L ≤	20
k (max.)	1.5
L (mm)	12
n	0.6
P	0.45
t (min.)	1

Technical Drawing

