



Slotted raised countersunk head screw DIN 964 Stainless steel A4 70 M3X6

Article number	55210.030.006
Brand	-
UBB	950353311497
UNSPSC	31161504
EAN	8715492336859
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	6 mm
Class	70
Driving features	Slotted
Head shape	Countersunk oval head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NEN	≈2371
ISO	≈2010
NF	≈E25-124
DIN	964
ASME	≈B18.6.7M
BS	≈4183

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
f ≈	0.75
Full thread if L ≤	22
k (max.)	1.65
L (mm)	6
n	0.8
P	0.5
t (min.)	1.2

Technical Drawing

