



Slotted raised countersunk head screw DIN 964 Stainless steel A4 70 M3X50

Article number	55210.030.050
Brand	-
UBB	950353554609
UNSPSC	31161504
EAN	8715492336972
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	50 mm
Class	70
Driving features	Slotted
Head shape	Countersunk oval head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

ASME	≈B18.6.7M
NEN	≈2371
ISO	≈2010
BS	≈4183
NF	≈E25-124
DIN	964

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
f ≈	0.75
Full thread if L ≤	22
k (max.)	1.65
L (mm)	50
n	0.8
P	0.5
t (min.)	1.2

Technical Drawing

