



Slotted raised countersunk head screw DIN 964 Stainless steel A4 70 M4X50

Article number	55210.040.050
Brand	-
UBB	950353554864
UNSPSC	31161504
EAN	8715492337115
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	50 mm
Class	70
Driving features	Slotted
Head shape	Countersunk oval head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

ISO	≈2010
NF	≈E25-124
BS	≈4183
DIN	964
ASME	≈B18.6.7M
NEN	≈2371

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
f ≈	1
Full thread if L ≤	25
k (max.)	2.2
L (mm)	50
n	1
P	0.7
t (min.)	1.6

Technical Drawing

