



Slotted raised countersunk head screw DIN 964 Stainless steel A4 70 M5X8

Article number	55210.050.008
Brand	-
UBB	950353313394
UNSPSC	31161504
EAN	8715492337146
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	8 mm
Class	70
Driving features	Slotted
Head shape	Countersunk oval head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

ASME	≈B18.6.7M
BS	≈4183
NF	≈E25-124
NEN	≈2371
DIN	964
ISO	≈2010

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
f ≈	1.25
Full thread if L ≤	30
k (max.)	2.5
L (mm)	8
n	1.2
P	0.8
t (min.)	2

Technical Drawing

