



## Hexagon socket set screw with dog point DIN 915 Stainless steel A4 M5X20

|                |               |
|----------------|---------------|
| Article number | 55230.050.020 |
| Brand          | -             |
| UBB            | 500571742815  |
| UNSPSC         | 31161518      |
| EAN            | 8715494117609 |
| PKG. of 500    | Full Box Only |

### Technical Parameters

|                    |                                                                                                    |
|--------------------|----------------------------------------------------------------------------------------------------|
| Diameter           | M5                                                                                                 |
| Length             | 20 mm                                                                                              |
| Driving features   | Hexagon socket                                                                                     |
| Material           | Stainless steel                                                                                    |
| Material technical | A4                                                                                                 |
| Thread direction   | Right                                                                                              |
| Point              | Dog                                                                                                |
| Thread             | Metric thread                                                                                      |
| Info               | These set screws are designed for pressure loads and are not suitable for tensile- or shear loads. |

### Standards

|      |          |
|------|----------|
| ISO  | 4028     |
| ASME | B18.3.6M |
| DIN  | 915      |
| NEN  | 2344     |
| NF   | E27-182  |
| BS   | 4168-4   |

### Technical Specification

|                |      |
|----------------|------|
| d-D            | M5   |
| dp (max.)      | 3.5  |
| L (mm)         | 20   |
| P              | 0.8  |
| s              | 2.5  |
| t (min.)       | 2    |
| z long (min.)  | 2.5  |
| z long if L ≥  | 8    |
| z short (min.) | 1.25 |

### Technical Drawing

