



Hexagon socket set screw with dog point DIN 915 Stainless steel A4 M5X25

Article number	55230.050.025
Brand	-
UBB	500571742997
UNSPSC	31161518
EAN	8715494117616
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	25 mm
Driving features	Hexagon socket
Material	Stainless steel
Material technical	A4
Thread direction	Right
Point	Dog
Thread	Metric thread
Info	These set screws are designed for pressure loads and are not suitable for tensile- or shear loads.

Standards

ISO	4028
DIN	915
ASME	B18.3.6M
BS	4168-4
NF	E27-182
NEN	2344

Technical Specification

d-D	M5
dp (max.)	3.5
L (mm)	25
P	0.8
s	2.5
t (min.)	2
z long (min.)	2.5
z long if L ≥	8
z short (min.)	1.25

Technical Drawing

