



Hexagon socket set screw with dog point DIN 915 Stainless steel A4 M10X30

Article number	55230.100.030
Brand	-
UBB	500571745057
UNSPSC	31161518
EAN	8715494117821
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	30 mm
Driving features	Hexagon socket
Material	Stainless steel
Material technical	A4
Thread direction	Right
Point	Dog
Thread	Metric thread
Info	These set screws are designed for pressure loads and are not suitable for tensile- or shear loads.

Standards

ASME	B18.3.6M
DIN	915
NEN	2344
NF	E27-182
BS	4168-4
ISO	4028

Technical Specification

d-D	M10
dp (max.)	7
L (mm)	30
P	1.5
s	5
t (min.)	4
z long (min.)	5
z long if L ≥	16
z short (min.)	2.5

Technical Drawing

