



Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A4 M2X20

Article number	55300.020.020
Brand	-
UBB	500633404479
UNSPSC	31161504
EAN	8715494623247
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M2
Length	20 mm
Class	70
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

NF	≈E25-119-1
ISO	≈7046-1
DIN	965

Technical Specification

d-D	M2
Thread length (min.)	16
dk (max.)	3.8
Full thread if $L \leq$	18
k (max.)	1.2
L (mm)	20
No. cross recess	1
P	0.4

Technical Drawing

