



Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A4 M3X18

Article number	55300.030.018
Brand	-
UBB	500633405047
UNSPSC	31161504
EAN	8715494623308
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	18 mm
Class	70
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

DIN	965
ISO	≈7046-1
NF	≈E25-119-1

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
L (mm)	18
No. cross recess	1
P	0.5

Technical Drawing

