



Cross recessed countersunk head screw Phillips DIN 965 A-H Stainless steel A4 M6X75

Article number	55300.060.075
Brand	-
UBB	500633406607
UNSPSC	31161504
EAN	8715494623469
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	75 mm
Class	70
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

DIN	965
ISO	≈7046-1
NF	≈E25-119-1

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
Full thread if L ≤	35
k (max.)	3
L (mm)	75
No. cross recess	3
P	1

Technical Drawing

