

Cross recessed countersunk head screw Pozidriv DIN 965 A-Z Stainless steel A4 M2,5X3



Article number	55302.025.003
Brand	-
UBB	500633407027
UNSPSC	31161504
EAN	8715494623506
PKG. of 1000	Full Box Only

Technical Parameters

Diameter (d-D)	M2,5
Length (L) (mm)	3
Material	Stainless steel
Head shape	Countersunk head
Driving features	Pozidriv
Thread	Metric thread
Material technical	A4

Standards

NF	E25-119-2
ISO	7046-2-Z
DIN	965 A-Z

Technical Specification

Thread length (min.)	18
d_k (max.)	4.7
Full thread if $L \leq$	20
k (max.)	1.5
No. cross recess	1
P	0.45

Technical Drawing

