



Cross recessed raised countersunk head screw Phillips DIN 966 A-H Stainless steel A4 M3X8

Article number	55320.030.008
Brand	-
UBB	500634462443
UNSPSC	31161504
EAN	8715494562140
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	8 mm
Class	70
Driving features	Phillips
Head shape	Countersunk oval head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

ISO	≈7047
NF	≈E25-120
DIN	966

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
f ≈	0.75
Full thread if L ≤	22
k (max.)	1.65
L (mm)	8
No. cross recess	1
P	0.5

Technical Drawing

