

Cross recessed raised countersunk head screw Phillips DIN 966 A-H Stainless steel A4 M3X16



Article number	55320.030.016
Brand	-
UBB	500634462773
UNSPSC	31161504
EAN	8715494562232
PKG. of 500	Full Box Only

Technical Parameters

Diameter (d-D)	M3
Length (L) (mm)	16
Material	Stainless steel
Head shape	Raised countersunk head
Driving features	Phillips
Thread	Metric thread
Material technical	A4

Standards

NF	E25-120
ISO	7047-H
DIN	966 A-H

Technical Specification

Thread length (min.)	19
d_k (max.)	5.6
$f \approx$	0.75
Full thread if $L \leq$	22
k (max.)	1.65
No. cross recess	1
P	0.50

Technical Drawing

