

Cross recessed raised countersunk head screw Pozidriv DIN 966 A-Z Stainless steel A4 M3X5



Article number	55322.030.005
Brand	-
UBB	500633414452
UNSPSC	31161504
EAN	8715494624244
PKG. of 1000	Full Box Only

Technical Parameters

Diameter (d-D)	M3
Length (L) (mm)	5
Material	Stainless steel
Head shape	Raised countersunk head
Driving features	Pozidriv
Thread	Metric thread
Material technical	A4

Standards

ISO	7047-Z
DIN	966 A-Z
NF	E25-120

Technical Specification

Thread length (min.)	19
d_k (max.)	5.6
$f \approx$	0.75
Full thread if $L \leq$	22
k (max.)	1.65
No. cross recess	1
P	0.50

Technical Drawing

