

## Hexalobular raised countersunk head screw DIN ≈966 A Stainless steel A4 M4X16



Article number	55325.040.016
Brand	-
UBB	500634464597
UNSPSC	31162400
EAN	8715494552882
PKG. of 500	Full Box Only

### Technical Parameters

Diameter (d-D)	M4
Length (L) (mm)	16
Material	Stainless steel
Head shape	Raised countersunk head
Driving features	Hexalobular
Thread	Metric thread
Material technical	A4

### Standards

ISO	≈14584
DIN	≈966 A

### Technical Specification

Thread length (min.)	22
$d_k$ (max.)	7.5
$f \approx$	1
Full thread if $L \leq$	25
$k$ (max.)	2.2
P	0.70
Socket	T20

### Technical Drawing

